






40-60min




"13"





**NIE PODNOSIĆ
BEZ MATERACA**





**POŁÓŻ MATERAC
PRZED PODNOSZENIEM**





1. Boki x2 +
belka środkowa x1





2. Szczyt x1




3. Wezgłowie x1




4. Dno pojemnika x2
















5. Rama podnoszona x1














6. Akcesoria x1




SWI6 x8  M6x60	SWI5 x4  M6x50	SWI4 x8  M6x40	SPK5 x36  M8x25
SM8-2 x12  M8x20	WW5-2 x4  5x30	WS4-3 x14  4x20	SPK7 x4  M8x35
BL4 x2  40x30mm	NS8 x4  M8	P8 x12 	P8D x8 
SR2 	MN x1L x1R 	BKK01 x4  125x125mm	PR-100-430 x2  300x40x30mm
PR-100-435 x2  300x40x30mm	PR-100-450 x1  300x30x30mm	PR-100-455 x1  300x30x30mm	KW x96 
L x48  L140 - 675mm L160 - 775mm L180 - 875mm	ST04 x 4 	SG x2  L140 - 1000N L160 - 1150N L180 - 1300N	KL4 x1  "4"









1)



2)




3)




OSTRZEŻENIE

Ustaw stopę tak, aby były w kontakcie z podłogą, gdy materac jest położony na ramę.



SM8-2 x4



M8x20

P8 x4




WW5-2 x4




5x30

1




3

P8




SM8-2

2




4



5


SM8-2
P8










6


x4

WW5-2






SM8-2 x8




M8x20

P8 x8





P8


SM8



DNO POJEMNIKA




PR-100-435



SWI6

KL4



WS4-3

x6

